

NETZSCH

Proven Excellence.



EPSILON Inline Disperser

The unique Dispersing System

Business Unit
GRINDING & DISPERSING

The unique System

FOR DISPERSING SOLIDS IN LIQUIDS

➤ NETZSCH *EPSILON* AS STANDARD VERSION

The NETZSCH *EPSILON* inline disperser is unique on the market. In the standard version, dispersion is not based on the conventional rotor-stator principle, in which high shear forces and a high energy input are used to disperse powder in liquid. In this version, the dispersing principle of the NETZSCH *EPSILON* does not use a stator through which the product flows and no narrow shear gaps between the rotating and stationary parts.



The pressure differences created by the pumping and centrifugal effect of the rotor are used to achieve the best possible wetting and dispersion of the powdered solids in liquid.

The resulting Advantages are:

- Minimal product heating
- Lowest input of shear forces
- Deaeration of the product after the solid intake
- Insensitive to small foreign objects
- High availability

Application Fields:

- Shear-sensitive products
- Temperature-sensitive products

➤ NETZSCH *EPSILON* AS A ROTOR-STATOR VERSION

For products that require dispersion with more energy, the NETZSCH *EPSILON* can also be equipped with a classic rotor-stator version. The dispersion principle is the same as in the standard version. Vacuum expansion of the contained air and wetting by overpressure also takes place here. However, the stator, through which the product flows, introduces significantly higher shear forces into the product.



The result is higher shear forces in the product for deagglomeration of powders that are difficult to disperse.

The Advantages of the Rotor-Stator Version:

- More intensive dispersion of agglomerates that are difficult to disperse
- Shorter dispersion time

Application Fields:

- Solids that are difficult to disperse
- Shear-insensitive products

YOUR BENEFIT

Dispersion Quality

- Consistently reproducible product quality
- Best wetting of the solid surface
- Gentle processing of sensitive formulation components

Handling & Cleaning

- Process free of manual influences
- Quick and easy to clean, good accessibility
- No adhesion of powder dust in the process tank

Dust & Emission Free

- Closed process housing
- Separate feeding of solid and liquid
- Loss-free incorporation of solids

Process Reliability


- Automatic mode eliminates operator error
- Tolerant to smaller foreign objects, generally, no machine downtime
- Explosion-proof version

Technical Data	<i>EPSILON 30</i>	<i>EPSILON 90</i>
Solids intake [kg/h]	50 - 5 000	150 - 12 000
Suspension flow during solids intake [m ³ /h]	15 - 30	40 - 80
Max. suspension flow during circulation [m ³ /h]	67 (water)	130 (water)
Drive power [kW]	30 / 37	75 / 90 / 110
Max. speed [1/min]	3 600	3 600
Max. discharge pressure [bar]	5	5
Min. feed pressure [bar]	0.1 - 0.5	0.1 - 0.5

Version of Execution



The *EPSILON* can be converted to the other version in a short time.



- 1 Barrier fluid system
- 2 Product outlet
- 3 Processing chamber
- 4 Powder inlet
- 5 Liquid inlet
- 6 Residual discharge
- 7 Mechanical seal
- 8 Frame
- 9 Motor
- 10 Control panel

Operating Principle

The *EPSILON* works together with a product tank in circulation. After the machine is started, the liquid flows to the *EPSILON* and is pumped back into the tank. Due to the strong pumping action of the rotor, a strong negative pressure is created in the process chamber of the *EPSILON*. This vacuum is used to draw in the powdered solids. No external vacuum generation or addition of external air is necessary. Powder that has been prepared in a hopper, silo, bag loading station or BigBag station is automatically drawn in by the machine when the powder feed is opened.

After the powder delivery, the powder feed is closed and, if necessary, circulation of the product continues. In this step, the enormous advantages of the dispersing system become clear: the subsequent dispersion improves the quality and simultaneously deaerates the suspension. Due to the low energy input, warming of the product is significantly reduced compared to conventional rotor-stator systems.




01 All powders contain air. The amount of air contained in the powder is the ratio of the bulk density to solid density and can be from 75 to more than 90 percent by volume. For a good dispersion result, this air must be completely replaced by liquid and the particles separated.

02 During the intake of the powder, the air contained in the powder expands in the negative pressure of the suction area. Loose agglomerates can break up at this point, while stronger agglomerates remain intact.

03 In the state of expanded air, the powder is drawn directly into the liquid and surrounded by it.

04 As the process continues, the powder enters the outer region of the process chamber in which there is a strong overpressure due to the centrifugal effect of the rotor. Here, the previously expanded air is strongly compressed and the surrounding liquid is forced into the core of the agglomerate structure.

05 Agglomerates wetted in this way can be dispersed with considerably less energy input. The desired fineness is achieved through subsequent dispersion, in which the product repeatedly passes through the negative pressure and overpressure region and is exposed to strong turbulence and micro-cavitation. The product is also automatically deaerated during subsequent dispersion. Air is drawn from the product in the negative pressure area and returned as large air bubbles to the tank, where they easily rise and outgas. Due to the gentle operation, significantly less energy is applied, in contrast to shear-based systems, so that even low temperature limits can be easily maintained.



NETZSCH Plant Construction & Application

Process Technology and Plant Construction


- Turnkey plant design, plant expansion and modernization using the latest machine and process technology.
- Project management from start to finish with performance guarantee.
- Worldwide customer service for spare parts, training, service and plant maintenance, etc.

System Integration

- Installation and operation on one level
- Compact dimensions
- Continuous batch production through, for example, combination with 2 or more process tanks and agitator bead mills

Options

- Connection for drawing in small quantities of liquid
- Residue drainage
- All optional connections can be operated manually or automatically
- Explosion-proof models for gas, dust and conductive dusts
- Integration into the customer's process control system
- Individual programming and process integration possible
- Remote maintenance service
- Noise protection enclosure



Digital Inkjet

- Very good printability
- Better open time
- Huge time savings when releasing photoinitiators
- Very good stability
- Easy to stay within temperature limits



Water-based Primer and Top Coat, Spray Coating

- Better fineness than conventional process
- Lower coarse fraction, better particle size distribution
- Deaeration of the product
- Easy to stay within temperature limits



Solvent-based Clear Coat, Semi-finished Product/ Incorporation of Fumed Silica

- Better fineness
- Easy to stay within temperature limits
- Deaeration of the product



Predispersion of Products for Grinding

- Optimal predispersion with very good wetting of the pigment surface
- Increase in the efficiency of the milling process through better wetting
- Consistent quality of predispersion, thus consistent conditions for the grinding process



APPLICATION EXAMPLES

The owner-managed NETZSCH Group is a leading global technology company specializing in mechanical, plant and instrument engineering.

Under the management of Erich NETZSCH B.V. & Co. Holding KG, the company consists of the three business units Analyzing & Testing, Grinding & Dispersing and Pumps & Systems, which are geared towards specific industries and products. A worldwide sales and service network has guaranteed customer proximity and competent service since 1873.

Proven Excellence.

Business Unit Grinding & Dispersing – The World’s Leading Grinding Technology

NETZSCH-Feinmahltechnik | Germany
NETZSCH Trockenmahltechnik | Germany
NETZSCH Vakumix | Germany
NETZSCH Lohnmahltechnik | Germany
NETZSCH Feinmahltechnik Polska | Poland
NETZSCH Mastermix | Great Britain
NETZSCH Broyage | France

NETZSCH España | Spain
NETZSCH Machinery and Instruments | China
NETZSCH India Grinding & Dispersing | India
NETZSCH Tula | Russia
NETZSCH Makine Sanayi ve Ticaret | Turkey
NETZSCH Premier Technologies | USA
NETZSCH Equipamentos de Moagem | Brazil

NETZSCH-Feinmahltechnik GmbH
Sedanstraße 70
95100 Selb
Germany
Tel.: +49 9287 797 0
Fax: +49 9287 797 149
info.nft@netzsch.com



NETZSCH®

www.netzsch.com